

HANDY GUIDE TO MIXING RENOLINE RESIN, ACTIVATOR AND ACCELERATOR

100mm – 4” RENOLINE (STRUCTURAL) SUPERLINER 2

Length (metre)	Resin (ltr) (minimum)	Maximum 3% at all times Activator (ml) (white liquid)	Minimum 2% Maximum 4%	
			Accelerator (ml) (clear liquid)	
			2%	4%
1	1.30	39	26	52
2	2.60	78	52	104
3	3.90	117	78	156
4	5.20	156	104	208
5	6.50	195	130	260
6	7.80	234	156	312
7	9.10	273	182	364
8	10.40	312	208	416
9	11.70	351	234	468
10	13.00	390	260	520

150mm – 6” RENOLINE (STRUCTURAL) SUPERLINER 2

Length (metre)	Resin (ltr) (minimum)	Maximum 3% at all times Activator (ml) (white liquid)	Minimum 2% Maximum 4%	
			Accelerator (ml) (clear liquid)	
			2%	4%
1	1.80	54	36	72
2	3.60	108	72	144
3	5.40	162	108	216
4	7.20	216	144	288
5	9.00	270	180	360
6	10.80	324	216	432
7	12.60	378	252	504
8	14.40	432	288	576
9	16.20	486	324	648
10	18.00	540	360	720

225mm – 9” RENOLINE (STRUCTURAL) SUPERLINER 2

Length (metre)	Resin (ltr) (minimum)	Maximum 3% at all times Activator (ml) (white liquid)	Minimum 2% Maximum 4%	
			Accelerator (ml) (clear liquid)	
			2%	4%
1	2.70	81	54	108
2	5.40	162	108	216
3	8.10	243	162	324
4	10.80	324	216	432
5	13.50	405	270	540
6	16.20	486	324	648
7	18.90	567	378	756
8	21.60	648	432	864
9	24.30	729	486	972
10	27.00	810	540	1080